






PRODUCT DESCRIPTION

Precisely stacked beveled Clear glass symmetrically positioned in a linear design evokes images of grand city skylines. As the bevels reflect light from within, above, and below, each facet and Polished Chrome surface takes on new depths and hues that draw the eye and inspire the senses. The architectural pattern brings a modern edge to a classic 1980s style.



MEASUREMENTS

DIMENSION	: 7.5" W x 9.5" H x 1" Ext
BACK PLATE	: 7.5" W x 9.5" H x 4.75" HCO
HANGING WEIGHT	: 2.16 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,000 Rated (930 Del.)
BULB	: 1 x 20W LED AC Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Antique Bronze (ANB)

Black (BK)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com