

## Q-Line Circuit Breakers

Cable-in Cable-out (lug-lug)

240V Class



TJD432400WL

### TQD 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number <sup>1, 2</sup> |
|------------|---------------|-----------------------------|--------------------------------|
| 2          | 100           | 10kA                        | TQD22100WL                     |
| 2          | 125           | 10kA                        | TQD22125WL                     |
| 2          | 150           | 10kA                        | TQD22150WL                     |
| 2          | 175           | 10kA                        | TQD22175WL                     |
| 2          | 200           | 10kA                        | TQD22200WL                     |
| 2          | 225           | 10kA                        | TQD22225WL                     |
| 3          | 100           | 10kA                        | TQD32100WL                     |
| 3          | 125           | 10kA                        | TQD32125WL                     |
| 3          | 150           | 10kA                        | TQD32150WL                     |
| 3          | 175           | 10kA                        | TQD32175WL                     |
| 3          | 200           | 10kA                        | TQD32200WL                     |
| 3          | 225           | 10kA                        | TQD32225WL                     |

### TQD 240 Vac, Internal Common Trip with Factory Installed 120 Vac Shunt Trip

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number <sup>1, 2</sup> |
|------------|---------------|-----------------------------|--------------------------------|
| 3          | 125           | 10kA                        | TQD32125ST1                    |
| 3          | 150           | 10kA                        | TQD32150ST1                    |
| 3          | 175           | 10kA                        | TQD32175ST1                    |
| 3          | 200           | 10kA                        | TQD32200ST1                    |
| 3          | 225           | 10kA                        | TQD32225ST1                    |

### THQD 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number <sup>1, 2</sup> |
|------------|---------------|-----------------------------|--------------------------------|
| 2          | 100           | 22kA                        | THQD22100WL                    |
| 2          | 125           | 22kA                        | THQD22125WL                    |
| 2          | 150           | 22kA                        | THQD22150WL                    |
| 2          | 175           | 22kA                        | THQD22175WL                    |
| 2          | 200           | 22kA                        | THQD22200WL                    |
| 2          | 225           | 22kA                        | THQD22225WL                    |
| 3          | 100           | 22kA                        | THQD32100WL                    |
| 3          | 125           | 22kA                        | THQD32125WL                    |
| 3          | 150           | 22kA                        | THQD32150WL                    |
| 3          | 175           | 22kA                        | THQD32175WL                    |
| 3          | 200           | 22kA                        | THQD32200WL                    |
| 3          | 225           | 22kA                        | THQD32225WL                    |

### TJD 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating          | 240 Vac Interrupting Rating | Product Number <sup>1, 2</sup> |
|------------|------------------------|-----------------------------|--------------------------------|
| 2          | 250                    | 22kA                        | TJD422250WL                    |
| 2          | 300                    | 22kA                        | TJD422300WL                    |
| 2          | 350                    | 22kA                        | TJD422350WL                    |
| 2          | 400                    | 22kA                        | TJD422400WL                    |
| 2          | 400 Molded Case Switch | 22kA                        | TJD422Y400                     |
| 3          | 250                    | 22kA                        | TJD432250WL <sup>3</sup>       |
| 3          | 300                    | 22kA                        | TJD432300WL <sup>3</sup>       |
| 3          | 350                    | 22kA                        | TJD432350WL <sup>3</sup>       |
| 3          | 400                    | 22kA                        | TJD432400WL <sup>3</sup>       |
| 3          | 400 Molded Case Switch | 22kA                        | TJD432Y400 <sup>4</sup>        |

<sup>1</sup>Refer to table on page 6-5 for lug and wire range data.

<sup>2</sup>Includes line and load lugs. For optional configurations see page 6-5.

<sup>3</sup>TJD uses same accessories as J600 line. TJD not listed HACR.

UL listed HACR (heating, air conditioning and refrigeration).