JET BLACK

JT1-1371
WWW.JETTOOLS.COM/JETBLACK



14SFX
14" BANDSAW
WITH JET BLACK PERFORMANCE COATING

5 YEAR WARRANTY

JET BLACK PERFORMANCE COATING

LOW FRICTION | RUST RESISTANT | MAINTENANCE FREE | ENHANCED VISIBILITY

POWER IN THE RIGHT HANDS

JWBS-14SFX-BLK
14" BANDSAW (1.75HP, 1PH, 115/230V)

SPECIFICATIONS

MODEL NUMBER	JWBS-14SFX-BLK
STOCK NUMBER	
Bandsaw Wheel Diameter (in.)	14"
Blade Speed (FPM)	3000
Wheel Speed (RPM)	765
Cutting Capacity Height (in.)	13"
Cutting Capacity Width (in.)	13-1/2"
Dust Port Diameter (in.)	4"
Dust Collection Minimum CFM Required (CFM)	400
Motor Phase	1
Motor Power (HP)	1.75
Motor Speed (RPM)	1720
Sound Emission without Load	75 dB at 3ft
Voltage (V)	115/230V (prewired 115V)
Recommended Circuit Size	20A (for 115V), 15A (for 230V)
Resaw Fence Size (L x W) (in.)	18-1/4" L x 6" H
Miter T-Slot (in.)	3/4"
Table Material	Cast Iron
Table Insert Material	Anodized Aluminum
Table Tilt	0° to 45°
Stand Type	Closed
Frame Material	Steel
Wheels	Cast Iron
Blade Guides	Ball Bearing Guides
Prop 65	Cancer and Reproductive Harm
Overall Assembled Dimensions (L x W x H) (in.)	37" x 27-1/2" x 75-3/8"
Footprint (L x W) (in.)	24-5/12" x 17-2/3"
Warranty	5 Year
Net Weight (lbs.)	272 lbs. (approx.)

OPTIONAL EQUIPMENT & ACCESSORIES

STOCK NUMBER	DESCRIPTION
JT9-708118	JMB-UMB Universal Mobile Base, 18" x 18" to 28" x 28"
JT9-714403	JWBS-14LIT Bandsaw Light Kit
JT9-JWBS14SFX-104	Push Stick
JT9-JWBS14SFX-300	Miter Gauge Assembly
JT9-WBSB-116124	Replacement Blade, 116" x 1/2" x 4 TPI
JT9-WBSB-116144	Replacement Blade, 116" x 1/4" x 4 TPI
JT9-WBSB-116583G	Replacement Blade, 116" x 5/8" x 3 TPI

OPTIONAL EQUIPMENT & ACCESSORIES


JT9-708118


JT9-714403



JT9-JWBS14SFX-104


PM9-PM1500-109


JT9-WBSB-116124


JT9-WBSB-116144


JT9-WBSB-116583G



JET BLACK PERFORMANCE COATING
Rust resistant, low-friction coating for more control.



TOP BLADE TENSIONING WHEEL
Provides better work piece clearance when cutting.



ADJUSTABLE BALL BEARING BLADE GUIDES
Reduces set up time and makes adjustments easier.



TILTING TABLE
Tilts up to 45° for making accurate angle cuts.



4" DUST PORT
Provides maximum dust collection for an optimal sawing experience.