Brasilia | E30271-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Inspired by the architecture of grand civic pavilions, the 304 grade stainless steel cages feature beveled arches that incorporate LED light sources along their frame. Finished in Matte Black, the simple yet distinctive geometry of the lanterns provide a transitional look that pairs well with both modern and transitional aesthetics.



MEASUREMENTS

DIMENSION	: 6.5" W x 12" H x 2.5" Ext
BACK PLATE	: 6.25" W x 11.75" H x 6" HCO
HANGING WEIGHT	: 3.28 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (550 Del.)
BULB	: 1 x 11W LED DC Integrated , 11W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 80 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)

MATERIAL

Stainless steel

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com