


RoHS COMPLIANT

REV	DATE
B	05/20/"21
C	08/18/"21




P/N	L	M	TIE-A	PE BAG	PE BAG 1/R	Q'TY
DBC-15FW-01	305±30	0.305		6"x8"x0.06MM	12"x14"x0.06MM 1/10	A/R
DBC-15FW-05	1525±50	1.525	100x2	6"x8"x0.06MM	14"x16"x0.06MM 1/10	A/R
DBC-15FW-10	3050±50	3.05	120x2	7"x10"x0.06MM	14"x16"x0.06MM 1/10	A/R
DBC-15FW-25	7625±50	7.625		8"x10"x0.06MM	16"x18"x0.06MM 1/5	A/R

PIN ASSIGNMENT

P1	P2	P1	P2
1 BLACK	P1	11 PINK	P11
2 BROWN	P2	12 LIGHT GREEN	P12
3 RED	P3	13 BLACK/WHITE	P13
4 ORANGE	P4	14 BROWN/WHITE	P14
5 YELLOW	P5	15 RED/WHITE	P15
6 GREEN	P6	S DRAIN CUT	
7 BLUE	P7		
8 PURPLE	P8		
9 GRAY	P9		
10 WHITE	P10		

*	LABEL: Prop 65 WARNING, 40*15MM	1	PCS
*	PE BAG: L"xW"x0.06MM	A/R	PCS
*	HT-TUBE OD:1.5MM, WHITE 15MM	15	PCS
*	TIE-A BLACK	XX*2	MM
*	CARTON: 46x30x25CM	A/R	PCS
*	PE BAG: 30"x28"x0.08MM	A/R	PCS
*	PE BAG: L"xW"x0.06MM	1	PCS
5	SCREW #4-40/BLACK	2	PCS
4	PVC BLACK (UL94-V0)	16	G
3	PVC-IN	4	G
2	D-SUB 15PIN FEMALE, BLACK	1	PCS
1	UL2464 28AWG 15C+AD BLACK OD:6.0	L	M
NO.	DESCRIPTION	QTY	UNIT



Part No.
DBC-15FW-XX

MODEL NAME:

D-Sub DB15 Female RS-232
Serial Cable to Lead Wires

MARK EXPLAIN:
Revision Change
Important Dimension
Note

TOLERANCE:
0.000:
0.00 : ±0.50
0.0 : ±0.50
0. : ±0.50
ANGLE: ±3.0°
UNIT: mm

CompuCableUSA