

COSTA BRAVA

513-36-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 31.75"

Width/Diameter: 36"

Minimum Height: 36.75"

Maximum Height: 108.75"

Canopy/Backplate: 8.5"

Hanging Type: 72" Chain

Product Weight: 33lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Natural Linen

Shade 1 Top Width: 12"

Shade 1 Height: 24.75"

Shade 2: Natural Woven

Shade 2 Finish: Coco Beads

Shade 2 Top Width: 12"

Shade 2 Height: 27"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 10

Bulb Included: No

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 40" x 34" x 32"

Carton 1 Weight: 59lb

Shipping Method: Truck Only

Country of Origin: PH

