

STONEY

F2524-PBR

The architectural design language of the Stoney family is softened by its unique material qualities. Large conical white linen shades are edged with contrasting whip-stitching, echoing the natural jute wrap details along the Patina Brass frames. Available as a 1-light sconce, 1-light pendant, 5-light chandelier, and 1-light floor lamp, Stoney is an ode to craftsmanship.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 21"

Width/Diameter: 24"

Minimum Height: 27.75"

Maximum Height: 69.75"

Canopy/Backplate: 5.5"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 6lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: White Linen

Shade 1 Top Width: 3.5"

Shade 1 Bottom L/W: 0" / 24"

Shade 1 Height: 14.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A21

Max Wattage: 25

Bulb Quantity: 1

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 26" x 26" x 18"

Carton 1 Weight: 14lb

Shipping Method: Ground

Country of Origin: VN

