Geist | E25193-BK


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



*max overall height

MEASUREMENTS

DIMENSION	: 35.5" L x 35.5" W x 19.5" H
MAX OAH	: 64" OAH
CANOPY	: 6.25" W x 2" H x 6.25" L
HANGING WEIGHT	: 31 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,780 Rated (2,700 Del.)
BULB	: 54W LED DC Integrated , 54W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Textured White (TW)

MATERIAL

Gypsum, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 15
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com