



FF1089PL



60.25" x 23.25" x 26.5" (H x W x D)

ENERGY STAR certified 24" wide 10.1 cu.ft. top mount frost-free refrigerator-freezer with reversible doors in a stainless steel look

Highlights:

- Over 10 cu.ft. of interior storage in a slim-fitting footprint
- ENERGY STAR qualified performance ensures annual savings
- True frost-free operation saves you maintenance by preventing icy buildup

Product Features:

24" Wide Top-Mount Refrigerator-Freezer	Over 10 cu.ft. capacity in a slim fit ideal for apartments and small kitchens
ENERGY STAR certified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
Frost-free operation	No-frost convenience for reduced user maintenance
Thin-line design	Limited space is no problem for our thin-line models, designed specifically for those hard-to-fit spots
Large capacity	10.1 cu.ft. interior offers generous storage in a slim fit
Stainless steel look	Doors offer the look of stainless steel complete with a vertical grain, but the easier cleanability of a fingerprint-resistant steel finish
Humidity controlled crispers	Twin crisper drawers offer the ideal storage conditions for produce, helping you to keep your fruits and vegetables separated
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Gallon door storage	Lower refrigerator door shelf can hold gallon-sized containers



FF1089PL Specifications:

Overview	
Nominal Height	60.0" (152 cm)
Height of Cabinet	59.63" (151 cm)
Height to Hinge Cap	60.25" (153 cm)
Nominal Width	24.0" (61 cm)
Width	23.25" (59 cm)
Width with Door Open	24.0" (61 cm)
Nominal Depth	27.0" (69 cm)
Depth	26.5" (67 cm)
Depth with door at 90°	48.0" (122 cm)
Capacity	10.1 cu.ft. (286 L)
Defrost Type	Frost-Free
Door	Stainless Look
Cabinet	Black
US Electrical Safety	CSA
Canadian Electrical Safety	CSA-C
Energy Usage/Year	297.0kWh/year
Amps	1.5
Voltage/Frequency	115 V AC/60 Hz
Weight	117.0 lbs. (53 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101087535
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	2
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	24.75" (63 cm)
Refrigerator - Interior Width	19.5" (50 cm)
Refrigerator - Interior Depth	21.0" (53 cm)
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2

Refrigerator - Full Door Shelves	1
Refrigerator - Half Door Shelves	4
Can Storage	Yes
Freezer - Interior Height	16.25" (41 cm)
Freezer - Interior Width	17.25" (44 cm)
Freezer - Interior Depth	17.0" (43 cm)
Freezer - Shelf Type	Glass
Freezer - Shelf Qty	1
Freezer - Full Door Shelves	1
Gallon Door Storage	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	1.73 oz.
Level Legs	2
Compressor Step Height	8.5" (22 cm)
Compressor Step Width	19.5" (50 cm)
Compressor Step Depth	7.0" (18 cm)
Sound Level	32.8 dB

