



North® Butyl™

13 Mil Butyl Rubber Glove with Rough Grip - 11"

- Exceptional resistance to a broad range of toxic chemicals: making it the only suitable for many critical applications.
- Highly resistant to ketones (MEK: MIBK: acetone) and esters (tricresyl phosphate: amyl acetate: ethyl acetate)
- Solvent based: multi-dip manufacturing process provides multiple layers of polymer (like a glove within a glove) which results in a glove of superior quality.
- Butyl provides the highest permeation resistance to vapors and gases
- Rough finish enhances grip on wet, oily or dry handling surfaces



Technical Data

Color	Black
Sizes Available	7-11
Polymer	Butyl
Thickness	13 Mil
Lining	Unlined
Dip	Single
Length	11"
Grip	Rough
Construction	Unsupported, Waterproof
Case Weight (lbs)	0.00
Packed	288 Pair/Case
Packaging	Bagged Pair
Certifications	TAA Compliant
Country of Origin	United States

Performance Data

EN 374-5	Bacteria and Fungi
----------	--------------------

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
B131R/7	Black	7	198987081324	10198987081321	20198987081328
B131R/8	Black	8	198987081300	10198987081307	20198987081304
B131R/9	Black	9	198987081317	10198987081314	20198987081311
B131R/10	Black	10	198987081331	10198987081338	20198987081335
B131R/11	Black	11	198987081348	10198987081345	20198987081342