

HARAC

B7811-PBR/BRZ

A classic RLM shade enhanced by industrial details and a mixed metal finish, the Harac sconce brings modern style to exterior walls and doorways. The Bronze finish is complemented by decorative elements like the knurled Patina Brass socket cup. Serving as a powerful downlight, Harac is available in two sizes to fulfill your outdoor lighting needs.

FINISHES

PATINA BRASS w/ BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 10.75"

Width/Diameter: 15"

Canopy/Backplate: 4.75"

Product Weight: 2.95lb

Extension: 17.25"

Top to Center: 2.5"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Acrylic

Shade 1 Finish: Clear

Shade 1 Top Width: 2"

Shade 1 Height: 0.75"

Shade 2: Aluminum

Shade 2 Finish: Bronze

Shade 2 Top Width: 15"

Shade 2 Height: 3"



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Bulb Type: LED

Max Wattage: 8

Bulb Quantity: 1

Bulb Included: Yes

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): No

Dark Sky: Yes

CRI: 90

Color Temp.: 3000k

Lumens: 425

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 18" x 20" x 14"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: CN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993

REVISED 3.11.2022