



Technical Data

Color	Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 10.24 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Malaysia
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Narrow Face
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Rubber Tips
Base Curve	11
Construction	Womans Fit
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

Bouton® Optical Eva® Petite

Rimless Safety Glasses with Clear / Pink Temple, Clear Lens and Anti-Scratch Coating

- Ensures a great fit for women with more slender facial profiles
- Better fitting eyewear will protect the eyes more effectively
- Lightweight, rimless design provides all day user comfort
- Pink rubber co-molded temples provide a secure fit
- Molded nose bridge design to fit the vast majority of users
- 11 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: ♻ Made from recycled or bio-based 🧼 Launderable ♻ Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-10

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-11-0900	Pink	Clear	Clear	AS	616314055652	01616314055651	02616314055650
250-11-0904	Pink	Tinted	Pink	AS	616314055676	01616314055675	02616314055674
250-11-0920	Pink	Clear	Clear	AS/AF	616314055669	01616314055668	02616314055667
250-11-5501	Pink	Tinted	Gray	AS	616314056017	01616314056016	02616314056015

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated