



Project / Job Name:

Location:

Fixture Type:

Notes:

S11697 - 15/11 Watt LED Direct Wire Downlight;
27K/3K/35K/4K/5K; 6-Inch; Dual Dimming; Round; with
Integrated Emergency and Test Switch



GENERAL

Company	SATCO
EA Height	6.89
EA Width	4.72
EA Length	8.27
Bulb Included	Integrated
Diameter	6.77
Material	Aluminum
Fixture Type	Remote Driver LED Downlight
Product Notes	Plenum Rated FT6 Cable; Integrated Emergency Driver and Test Switch; Fixture produces 500lm under emergency battery power; Wattage increases by 5W during charging periods.
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	<30%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	Default Wattage: 15W; Battery Weight: 0.62lbs
Amps	0.092-0.040/0.125-0.054A
Integrated Features	Emergency and Test Switch
Lens Finish	Matte Frosted
Lens Material	Acrylic
Lensed	Yes
Nominal Length	6.0
Power Factor	>0.9
SDS Class	Lithium_Ion_Battery
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	85W

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	108
Color Temp	Warm White to Natural Light
CRI	90+
Dimming Type	Dual Dimming, Forward (TRIAC) or Reverse Phase at 120V/0-10V at 120-277V
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	1350L/1050L
Volts	120V-277V
Watts	15W/11W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
Housing Color	White
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	5-Years
----------	---------

FEATURES

Flicker Free	Yes
--------------	-----

PACKAGING

UPC	045923116971
Case Cube	2.1555
Case Height	14.57
Case Length	17.32
Case Quantity	12
Case UPC	10045923116978
Case Weight	43.22
Case Width	14.76
EA Cube	0.1556
EA Height	6.89
EA Length	8.27
EA Quantity	1
EA Weight	3.42
EA Width	4.72
Pack Type	Color Box
Web Height	1.34
Web Width	6.77

COMPLIANCE

ADA Compliant	No
Air Tight	Yes
CA Prop 65	Lead
Dark Sky Rated	No
Energy Star ID	4517253
FCC Compliant	Yes
IC Rated	Yes
IP Rating	IP44
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Certified
California Ban	Lawful for sale
Energy Star Certified	Yes
Title 20	Yes
T24/JA8 Compliant	Yes