# **Syndicate** | E21384-18BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








## PRODUCT DESCRIPTION

Segmented by bright LED rings finished in Matte Black, glass shades of an hourglass shape are combined into various configurations. The hand-blown glass is entirely transparent and varies in size creating an undulating pattern. All together, the series includes pendants, flush mounts, and portable lamps.




### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 8.75" L x 8.75" W x 44.25" H |
| MAX OAH | : 88" OAH |
| CANOPY | : 5.75" W x 1.75" H x 5.75" L |
| HANGING WEIGHT | : 23.1483 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 1,800 Rated (1,350 Del.) |
| BULB | : 4 x 9W LED DC Integrated , 36W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : 3-in-1: Triac, ELV, or 0-10V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |

### FINISHES OPTION

Black (BK)

### GLASS

Clear 18

### MATERIAL

Aluminum,Steel,Glass

### RATINGS

cETLus
Dry Location

### ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com