

LENNOX

B3011-PBR

Crafted from walnut wood and Patina Brass, this spotlight sconce combines functional articulation with a natural, handcrafted feel. Its slim cylindrical head pivots within the U-shaped cuff, which itself rotates at the backplate to provide a complete range of motion. The elevated mix of materials demonstrates that peak utility doesn't confine aesthetics.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 11"

Width/Diameter: 5"

Canopy/Backplate: 5"

Product Weight: 3lb

Extension: 8.5"

Top to Center: 4.25"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Wood

Shade 1 Finish: Wood

Shade 1 Top Width: 3.25"

Shade 1 Bottom L/W: 0" / 3.25"

Shade 1 Height: 10.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: GU10

Bulb Type: MR16

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: TWISTED BROWN FABRIC

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 12" x 9" x 13"

Carton 1 Weight: 7lb

Shipping Method: Ground

Country of Origin: VN

