




TEGERA® 846

Learn more

EXTRA-LONG CUFF FOR EXTRA PROTECTION

A disposable nitrile glove with extra-long cuff for extra protection. It has a good fit and a light texture for a good grip. 0,19 mm/7,4 mil, non-powder, latex-free and approved for handling food stuffs. Suitable for applications in the automotive industry and other kinds of precision work. 50 pieces/bag. 10 bags/carton.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Good fit
- Comfortable

FUNCTIONS

- Approved for handling foodstuffs
- For touchscreen
- Extra long
- Latex-free
- Oil and grease resistant
- Waterproof

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Risk of infection, Contact with dirt, Contact with moisture, Contact with damp, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Microbiological risk environments, Disposable use, Wet environments, Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Fishing industry work, Food handling, Kitchen work, Hotel- and restaurant work, Cleaning, Service work

PRIMARY INDUSTRIES OF USE

Accommodation and food service (HoReCa), Facility management services, Oil and gas extraction, Food and beverage processing, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Light weight

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Disposable gloves - General protection
CATEGORY Cat. III
THICKNESS 0,19 mm
LENGTH 290 mm
INSIDE Non powder
COLOUR Blue
QUANTITY PER PACK 50 Pieces
PACKS PER: BUNDLE/CARTON Not sold in bundle/10
AQL 1.5
DISPLAY TYPE Bag
DIPPING MATERIAL Nitrile
CUFF STYLE Rolled edges

COMPLIANCE

CE 2777

UKCA 0321

EAC

TP TC 019:2011

EN ISO 21420:2020

EN ISO 374-5:2016 Virus

EN ISO 374-1:2016+A1:2018 Type B
JKOPT

FDA compliant material

FEATURES

General Protection

For touchscreen

Waterproof

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	J	K	O	P	T
Permeation level	3	6	2	3	5
Degradation %	37,3	-12,2	-8,4	-6,6	2,8

SIZE		ARTICLE NUMBER	EAN
6	XS	846-6	7392626073982
7	S	846-7	7392626074002
8	M	846-8	7392626074026
9	L	846-9	7392626074040
10	XL	846-10	7392626073920
11	XXL	846-11	7392626073944
12	3XL	846-12	7392626073968

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.