



Project / Job Name:

Location:

Fixture Type:

Notes:

S14403 - 13.5/10/5 Watt LED A19 Three-Way L amp;
3000K CCT; Lumens Selectable; Medium Double Contact
Base; Plastic; 120 Volt; 1-Pack



GENERAL

Company	SATCO
EA Height	4.73
EA Width	2.4
EA Length	2.4
Material	Plastic
Fixture Type	3-Way
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<150%
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Additional Info	Default Wattage: 13.5W; Three Way Lamp
Amps	0.182A
IOT Enabled	No
Lens Finish	Frosted
Lens Material	Plastic
Lensed	Yes
Operating Position	Universal
Power Factor	>0.5
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	100W/70W/30W

ELECTRICAL

CCT (Kelvin Temp)	3000K
Dimmable	Non-Dimmable
Hours Rated	15000
Beam Angle (degree)	230
Color Temp	Soft White
CRI	90+
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	1100L/800L/450L
Volts	120v
Watts	13.5W/10W/5W

PHYSICAL

Lamp Base	Medium Double Contact
Finish	Frost
Housing Color	White
ANSI Base	E26d
Lamp Type	A19
MOD Lamps	2.36
MOL	4.53

ADDITIONAL INFO

Warranty	2-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes
--------------	-----

PACKAGING

UPC	045923144035
Case Cube	0.5907
Case Height	11.19
Case Length	11.03
Case Quantity	24
Case UPC	10045923144032
Case Weight	4.32
Case Width	8.27
EA Cube	0.0158
EA Height	4.73
EA Length	2.4
EA Quantity	1
EA Weight	0.13
EA Width	2.4
Inner Cube	0.1153
Inner Height	5.12
Inner Length	7.6
Inner Quantity	6
Inner UPC	20045923144039
Inner Weight	0.9
Inner Width	5.12
Pack Type	Color Box
Web Length	4.53
Web Width	2.36

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Yes
T24/JA8 Compliant	No