Nucleus | E25153-BKNAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Thick Clear glass orbs suspend elegantly, each encasing a small aluminum sphere encompassed within. Discretely recessed, dedicated LEDs provide ample lighting without glare. The multi-light pendants feature three orb sizes branching out from a central structural column, which also includes a direct downward-facing LED. A striking Black and Satin Brass combination adds sophistication, making these atomically inspired fixtures bold statement pieces.



*max overall height

MEASUREMENTS

DIMENSION	: 9" W x 9.75" H
MAX OAH	: 133" OAH
CANOPY	: 6" W x 1.88" H x 6" L
HANGING WEIGHT	: 3.66 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 600 Rated (700 Del.)
BULB	: 1 x 10W LED AC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black / Natural Aged Brass (BKNAB)

MATERIAL

Steel + Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 70
RATED LIFE 40000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com