



PIP®

Small Reusable TPR Corded Ear Plugs - NRR 25

- 20% smaller than traditional reusable ear plugs for a better fit in smaller ear canals
- Pre-formed plug shape with no rolling required makes insertion simple
- Self-sealing flanges give all day comfort
- Rigid stem makes insertion easy and reduces the risk of contamination
- Can be reused several times, making them very cost efficient
- Moderate attenuation allows for safe usage that blocks out hazardous noise yet allows warning signals and voices to be clearly understood
- Cord can be detached for added safety when working around machines, or when the TPR plug is to be cleaned using soap and water

Technical Data

Color	Orange
Sizes Available	S
Packaging	Boxed
Packed	10 Boxes/Case
Case Dimensions (in)	21.37 x 16.38 x 9.62
Case Weight (lbs)	9.35
Country of Origin	Mexico
Hearing Style	Corded
Ear Plug Material	Thermoplastic Rubber
Shape	Flange
Cord Material	Textile
Box Count	100
Certifications	TAA Compliant
Product Circularity	Reusable / Launderable

Performance Data

NRR Rating (ANSI S3.19-1974)	25
SLC 80 Class	Class

Care Instructions

After use, clean and disinfect the plugs with mild soap and warm water. Let plugs dry before reuse. The ear plugs should be regularly inspected for serviceability.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
267-HPR330C	Orange	S	616314725449		20616314725443