

BIRK

RTL7914-PBR/BRZ

Combining the classic with the cool, the Birk family blends sleek architectural lines with an understated RLM shade to create a convenient exterior lighting solution. Featuring two wall-mounted sconces and a portable, battery-powered table lamp, the designs reflect LED light downward after it bounces off the shallow dome shade. The integrated handle of the table lamp encourages portability, making it perfect to carry both indoors and outdoors. Birk is finished in Bronze with Patina Brass accents.

FINISHES

PATINA BRASS w/ BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 13.75"

Width/Diameter: 11"

Canopy/Backplate: 3.25"

Product Weight: 3.74lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Glass

Shade 1 Finish: Clear Inside Etched

Shade 1 Top Width: 2.5"

Shade 2: Aluminum

Shade 2 Finish: Bronze with Soft White Inside

Shade 2 Top Width: 11"

Shade 2 Height: 1.75"



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 2

Bulb Quantity: 1

Bulb Included: No

Switch Type: FULL RANGE DIMMER ON
FIXTURE

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 3000k

Lumens: 50

Title 24: No

Field Serviceable: No

Battery

Battery Powered: Yes

Battery Included: Yes

Battery Life: 12-15 Hours

SHIPPING

Carton 1: 13" x 13" x 11"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: CN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993

REVISED 3.11.2022