

ART VERSION #: 3

ART REVISION DATE: 04/22/2016

FINAL ART DATE: 04/00/2016

SPEC #: A01-I126-0769 A

PART #: 3235 827026 01

269.0

134.0

135.0

100.0

Lighting Facts Per Bulb, **Brightness** 200 lumens, **Estimated Yearly Energy Cost** \$0.24 (Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use), **Life** 13.7 years (Based on 3 hrs/day), **Energy Used** 2.0 watts, **Light Appearance** 3000 K

LIMITED WARRANTY: Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 3 years based on up to 3 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund your original purchase price upon receipt of the returned bulb, register receipt and proof of purchase. Please call our toll-free number, write to Philips or send an email at the website below to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. **REPLACEMENT OR REFUND IS YOUR SOLE REMEDY. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED.** Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

WARNINGS AND CAUTIONS: Not suitable for use with dimmers. Suitable for use in open fixtures (luminaires). This device is not intended for use with emergency exit fixtures or emergency lights. Risk of electric shock - Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. Only install in operating environments between -4°F and +95°F (-20°C and +35°C).

NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.

Any Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This Class B complies with Canadian ICES-005.

Información sólo para el mercado mexicano
Lámpara LED Direccional bulbo T5 2W
Tensión Eléctrica 12V~
Frecuencia 60Hz
Corriente Eléctrica 290mA

Importado y/o Distribuido por:
PHILIPS MEXICANA S.A DE C.V. Av. La Palma No. 6
Col. San Fernando La Herradura
Huixquilucan Estado de México CP. 52784
R.F.C. PME-620620-E84

Línea de Atención al Cliente
01800 508 9000 | (55) 5269 9139
smartlight.mexico@philips.com
Garantía 3 años, para términos y condiciones consultar el siguiente link:
<http://www.lighting.philips.com.mx/connect/garantias.wpd>
Ensamblado en alguno de los siguientes países:
China y/o Mexico

Philips Lighting North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873, USA
Questions or Comments:
1-800-555-0050 www.philips.com
Made or assembled in one or more of the following countries: China, Mexico

3235 827026 01
Ordering Code:
BC2T5/AMB/830/ND Wedge 12V 2PK
Model: 9290012370

BACK

PHILIPS LIGHTING USA

Brand	PHILIPS
Product Family	LED
Shape	T5
Wattage	2
Master Brand Template Ref.	3235 827008 01
SGS number	XXXXXXXX
6NC #	463455
PKG PART #	3235 827026 01
DIE #	3241 648 47451
CRC #	CRC_XXXUS

Barcode No. **046677463458**

Operator(s) **donna.raia@philips.com**

v3

VERSION No.

Date **April 6, 2016**

Cyan

Magenta

Yellow

Black

Die

Die

Date Check _____

Check briefing Traffic

Artwork document

Legend Number of colors
 12NC Trapping/Bleed
 Barcode Images hires
 Diecut Jobsizes

Approval

QC Lithographer _____
 Product Manager _____
 Traffic Manager _____

FRONT