



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

S14219 - 5.5 Watt C11 LED; 2000K CCT; Candelabra Base; Clear Glass; Amber coil Filament; Dimmable; 120 Volt



GENERAL

Company	SATCO
EA Height	4.35
EA Width	1.56
EA Length	1.56
Dimmable Text	Forward or Reverse Phase; Line Voltage
Lamp Filament	Spiral
Material	Glass
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	<75%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Clear
Amps	0.070A
Lens Material	Glass
Operating Position	Universal
Power Factor	>0.7
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	40W

ELECTRICAL

CCT (Kelvin Temp)	2000K
Dimmable	Yes-Dimmable
Hours Rated	15000
Beam Angle (degree)	300
Color Temp	Warm White
CRI	90+
Dimming Type	Linear Dimming, Phase cut
Operating Frequency	60Hz
Operating Temp	-25C (-13F) to +40C (+104F)
Lumens	500L
Volts	120v
Watts	5.5W

PHYSICAL

Lamp Base	Candelabra
Finish	Clear Amber
ANSI Base	E12
Lamp Type	C11
MOD Lamps	1.38
MOL	3.92

ADDITIONAL INFO

Warranty	2-Years
Rated For Enclosed Fixture	Yes

PACKAGING

UPC	045923142192
Case Cube	0.2488
Case Height	5.28
Case Length	10.99
Case Quantity	24
Case UPC	10045923142199
Case Weight	2.07
Case Width	7.41
EA Cube	0.0061
EA Height	4.35
EA Length	1.56
EA Quantity	1
EA Weight	0.06
EA Width	1.56
Inner Cube	0.0506
Inner Height	4.96
Inner Length	5.08
Inner Quantity	6
Inner UPC	20045923142196
Inner Weight	0.43
Inner Width	3.47
Pack Type	Color Box
Web Length	3.92
Web Width	1.38

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
Title 20	Exempt
T24 Compliant	No