Project / Job Name:

Location:

Fixture Type:

Notes:



67-530 - Running Man Green Edge Lit Exit Sign; 120-347V; 2HR backup; Single/Dual Face; Universal Surface or Recessed Mounting; Pivoting Panel; Brushed Aluminum Finish

DAMP LOCATION

RoHS COMPLIANT

GENERAL

Company	SATCO
EA Height	8.66
EA Width	4.72
EA Length	18.5
Bulb Included	Integrated
Material	Aluminum
Fixture Type	Exit Sign
Product Notes	Ni-Cad Battery; 120 minute discharge time
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	120%-140%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Metallic
Amps	0.028-0.009A
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Acrylic
Power Factor	0.38
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5700K
Dimmable	Non-Dimmable
CRI	80+
Operating Frequency	60Hz
Operating Temp	+50F to +104F (+10C to +40C)
Volts	120V-347V
Watts	3W
Battery Chemistry	Ni-Cad

PHYSICAL

Lamp Base	Integrated
Finish	Brushed Aluminum
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Universal

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923675867
Case Cube	1.5338
Case Height	9.25
Case Length	18.9
Case Quantity	3
Case UPC	10045923675864
Case Weight	22.49
Case Width	15.16
EA Cube	0.4376
EA Height	8.66
EA Length	18.5
EA Quantity	1
EA Weight	6.39
EA Width	4.72
Pack Type	Box
Web Height	10.57
Web Width	18.23

COMPLIANCE

CA Prop 65	Lead
IP Rating	IP40
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	CSAus
California Ban	Non-Compliant
Title 20	No
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026