

VARENNA

502-34-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 22.5"

Width/Diameter: 34"

Canopy/Backplate: 23.5"

Product Weight: 145.2lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Piastre

Shade 1 Top Length: 3.75"

Shade 1 Top Width: 1.5"

Shade 1 Height: 11"

Shade 2: Glass

Shade 2 Finish: Piastre

Shade 2 Top Length: 3.75"

Shade 2 Top Width: 1.5"

Shade 2 Height: 12.75"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 15

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 42" x 36" x 23"

Carton 1 Weight: 171lb

Shipping Method: Truck Only

Country of Origin: PH