Hemisphere | E24906-GBGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Constructed of double thick aluminum which has a hammered interior finish polished so to not only be beautiful but multiply the lumen output. High polish enamel paints finish the exterior for the ultimate reflective surface. The larger sizes are fitted with commercial grade LED and multi-volt input drivers that dim with both ELV and 0-10V functions.



*max overall height

MEASUREMENTS

DIMENSION	: 31" L x 31" W x 17" H
MAX OAH	: 136" OAH
CANOPY	: 8" W x 1" H x 8" L
HANGING WEIGHT	: 12.3 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,900 Rated (1,440 Del.)
BULB	: 1 x 30W LED PCB Integrated , 30W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Gloss Black / Aluminum (GBAL)
- Gloss Black / Gold (GBGLD)
- Gloss Navy / Aluminum (GNAL)
- Gloss Taupe / Aluminum (GTAL)
- Gloss White / Aluminum (GWAL)

MATERIAL

Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 30
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com