

YS36L, Compression Splice, 600 kcmil Cu, Standard Barrel

By Burndy
Catalog # [YS36L](#)



600 kcmil, CU, Standard Barrel SPLICE

Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	600 kcmil
Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str	600
Compact Size	
Conductor Size	600 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	600 kcmil

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	82 mm
mm	
Dimension - Strip Length inch	1-7/16
Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Length Overall	3.22 in
inch	

General

Trade Name	HYLINK™
Die Index	22
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Green
Sub Brand	HYLINK
UPC	781810526408
Type	YS-L, Standard Barrel
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810526408
UPC 14 Digit GTIN	00781810526408

Logistics

Minimum Pack Quantity	1
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)