



EAN:	4013288101310	Size:	105x55x14 mm
Part number:	05104610001	Weight:	11 g
Article number:	848 HSS	Country of origin:	CN
		Customs tariff number:	82075060

- Twist bit for metal applications
- Hex shaft for very good power transfer
- HSS = high speed steel with split point
- Finely-tuned material elasticity for great durability
- Very good concentricity

High quality metal twist drill bits for precise drilling in metal. Made out of high speed steel (HSS). A finely-tuned material elasticity provides for a long service life. Very good concentricity. Tough viscous tempered bits ensure a particularly long service life. The hexagonal shaft ensures very good power transfer. Drive: 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

Web link

<https://www.wera.de/en/05104610001>

Wera - 848 HSS

05104610001 - 4013288101310

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de




Twist drill bits for metal applications



Twist drill bits - for metal applications

- 1/4" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173)
- Hexagon shaft for very high torque transfer
- HSS = high speed steel with cone point
- Finely adjusted material elasticity for long service life
- Excellent concentricity
- Tough-absorbing tempered bits for particularly long service life

Further versions in this product family:

			
	mm	mm	mm
05104610001	3.0	16.00	38.0
05104611001	3.1	18.00	40.0
05104612001	3.3	18.00	40.0
05104613001	4.0	20.00	44.0
05104614001	4.1	20.00	44.0
05104615001	4.2	20.00	45.0
05104616001	5.0	26.00	50.0
05104617001	5.1	26.00	50.0
05104618001	6.0	26.00	50.0
05104619001	6.8	30.00	50.0
05104620001	8.0	32.00	51.0
05104621001	8.5	33.00	53.0
05104622001	10.0	38.00	54.0

Web link

<https://www.wera.de/en/05104610001>

Wera - 848 HSS
 05104610001 - 4013288101310

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de