

Project Name

Location

Prepared By



## NUVO 62-1881

LED GLAMOUR BN 32" OVAL

**Notes**

[www] 06-11-2023 09:31:01

**General**

Status	Active
Collection	Glamour
Finish	Brushed Nickel
Wattage	50W
Style	Transitional
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Length (in.)	32.2
Width (in.)	17.99
Height (in.)	4.34
Indoor or Outdoor Fixture	Indoor

**Smart Product Info**

IOT Enabled	No
Integrated Camera	No

**Specifications**

Technology	LED
CRI	90+
Lumen Output	3133L/3256L/3555L/3661L/3690L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	6.65
Fixture Shape	Oval
Fixture Material	Steel
Fixture Type	Flush Mount
Operating Temperature	-20C (-4F) to +40C (+104F)

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Warranty	5-Years
----------	---------