Project / Job Name:

Location:

Fixture Type:

Notes:



65-697 - 2X4 Emergency Backup; Double Basket LED Troffer Fixture; Wattage Selectable; CCT Selectable; Lumens Selectable; White Finish

GENERAL

Company	NUVO
EA Height	25.71
EA Width	4.33
EA Length	49.49
Bulb Included	Integrated
Material	Steel
Fixture Type	Double Basket Troffer
Status	Active
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	90 Minute Battery Runtime
Amps	0.300-0.108/0.400-0.144/0.500-0.181A
Has Camera	No
Integrated Features	Integrated Battery Backup
IOT Enabled	No
Lens Material	Poly methyl methacrylate (PMMA)
Power Factor	0.9
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	125W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Neutral White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-4F to +104F (-20C to +40C)
HID Equivalent	70W-125W
Lumens	3300L-5750L
Volts	120V-277V
Watts	30W/40W/50W
Max Lumens	5750L
Battery Chemistry	Lithium-ion (Li-ion)

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923655258
Case Cube	3.1883
Case Height	25.71
Case Length	49.49
Case Quantity	1
Case UPC	10045923655255
Case Weight	16.1
Case Width	4.33
EA Cube	3.1883
EA Height	25.71
EA Length	49.49
EA Quantity	1
EA Weight	16.1
EA Width	4.33
Pack Type	Box
Web Height	3.02
Web Length	47.72
Web Width	23.74

COMPLIANCE

CA Prop 65	Lead
DLC ID	S-MTPRWN
FCC Compliant	Yes
IC Rated	Yes
IP Rating	IP20
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
UL Application	LED Recessed Luminaire/Type IC
DLC Approved	Yes
Title 20	Yes
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026