



2101XX

Technical Data

Color	Black
Sizes Available	9.75-10.5
Packaging	Boxed
Packed	32 Pair/Case
Case Dimensions (in)	33.50 x 25.50 x 26.50
Case Weight (lbs)	64.00
Country of Origin	United States
Polymer	Neoprene
Grip	Smooth
Length	32"
Powder	Powder Free
Thickness	15 Mil
Construction	Waterproof, Supported
Certifications	21 CFR, TAA Compliant

North®

15 Mil, 8" Port Ambidextrous Neoprene Glovebox Glove - 32"

- Neoprene is a soft flexible material that provides high permeation resistance to vapors and gases while also providing resistance to a broad range of chemicals like oils, greases, fuels, and acetones
- Neoprene offers good elongation and high flexibility for free movements when working inside of the box
- Complies with USDA and FDA regulations, 21 CFR, for use in food processing
- Rolled bead cuff resists tearing, improves donning strength and maintains a secure seal on glovebox ports
- Smooth finish for low friction, improved dexterity, and precise glovebox handling
- Available in 9.75" and 10.5" sizes (palm diameter)
- Ambidextrous construction allows for use with either hand
- Made in the USA

Care Instructions

Three year shelf life when stored in original packaging in a cool dry place away from light. Recommended temperature range: 50F to 86F (10C to 30C).

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
8N1532A/9Q	Black	9.75	883940165721		00883940165486
8N1532A/10H	Black	10.5	883940165714		00883940165479