Nimbus | E11525-113BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Oblong glass globe shades feature a intriguing Marble swirl pattern that obscures the integrated LED lighting within. Thin black electrical cords are easily adjustable. A larger oval 8-Light configuration features multiple sizes of the glass to create an interpretative congregation of clouds. Also available as a 3-Light, 5-Light and single pendant.



MEASUREMENTS

DIMENSION	: 26.25" L x 26.25" W x 8" H
MAX OAH	: 127.5" OAH
CANOPY	: 20.5" W x 1.5" H x 20.5" L
HANGING WEIGHT	: 22 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,800 Rated (3,400 Del.)
BULB	: 5 x 7W LED DC Integrated , 35W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

GLASS

White Cirrus 113

MATERIAL

Aluminum, Steel, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 15
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com