

TIRANA

480-54-VGL

While simplistic, the natural silk shades and circular motifs of the Tirana family nod to a nautical spirit. The conical shades provide a contemporary lightness to the traditional silhouettes. By contrast, the delicately textured Vintage Gold Leaf metalwork catches the light like a modish bangle bracelet. Available as a 1-light sconce and a 12-light, 15-light, and 27-light chandelier, Tirana produces warm, refined lighting for transitional spaces.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 13.5"

Width/Diameter: 54.75"

Minimum Height: 28.75"

Maximum Height: 71.25"

Canopy/Backplate: 7.75"

Hanging Type: 72" Chain

Product Weight: 20.9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Fabric

Shade 1 Finish: Natural Silk

Shade 1 Top Width: 2.25"

Shade 1 Bottom L/W: 0" / 5.5"

Shade 1 Height: 10"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 15

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 56" x 56" x 15"

Carton 1 Weight: 58lb

Shipping Method: Truck Only

Country of Origin: PH