



**SUREGRIP®
UNIVERSAL BORDER ADHESIVE**

DESCRIPTION AND USES

Zinsser® SureGrip® Universal Border Adhesive hangs pre-pasted, non-pasted and paste-the-wall (non-woven) borders over any wallpapered or painted surface. SureGrip is a mildew-resistant product which provides excellent adhesion while making for easy removal at a later time.

PERFORMANCE CHARACTERISTICS

- Goes on pink and dries clear
- Non-staining formula cleans up with water
- Eliminates the need for water-trays, primer and sizing
- Makes future border removal quick and easy

PRODUCTS

SKU	DESCRIPTION
2872	1-Gallon
2874	1-Quart
2876	16 Fluid Ounces

PRODUCT APPLICATION

SURFACE PREPARATION

Surfaces should be clean, dry, sound and free of dust, grease, wax, oil, old wallcovering adhesive, mold and mildew and other residue. Inspect the surface for paint bonding, loose wallcoverings, damaged wallboard or plaster. Remove old or loose wallcovering and residual wallcovering adhesive with DIF® Wallpaper Stripper. Repair unsound surfaces. Seal loose paint or damaged drywall and fully cured skim coats with Gardz® High Performance Sealer as needed.

PRODUCT APPLICATION (cont.)

ENVIRONMENTAL CONDITIONS

The recommended temperature range for application is between 50-85°F (10-29°C) with less than 50% relative humidity.

APPLICATION

SureGrip Universal Border Adhesive has a unique pink color that helps you see exactly where the adhesive has been applied, which helps to eliminate missed spots and edges. Color disappears completely when dry. Make sure sufficient adhesive is applied at edges and corners. Use full strength. **Do Not Dilute.**

“Paste-the-Wall” Non-woven Borders – Using the applicator on the 16 ounces bottle or a high quality 3 or 4 inch brush for the bulk containers, apply the paste directly to the wall. While the paste is wet, hang borders according to the manufacturer’s directions.

Pre-pasted and Non-pasted Borders – Apply directly to back and book according to the manufacturer’s directions before hanging.

COVERAGE

SureGrip Universal Border Adhesive will hang 4-6 spools of 6” border. Spread rate may differ with various backings.

CLEAN-UP

Wipe off excess adhesive from the border surface and surrounding areas with a damp sponge after each piece is installed. Blot dry with a soft towel. Change water often. Clean tools with warm water.



**SUREGRIP®
UNIVERSAL BORDER ADHESIVE**

PHYSICAL PROPERTIES

		SUREGRIP UNIVERSAL BORDER ADHESIVE
Resin Type		Vinyl Acetate Copolymer and Crotonic Acid
Solvents		Water
Weight	Per Gallon	8.45 lbs.
	Per Liter	1.01 kg
Solids	By Weight	7.5%
	By Volume	6.0%
Volatile Organic Compounds		<60 g/l (0.50 lbs./gal.)
Practical Coverage at Recommended DFT (assumes 15% material loss)		4-6 spools of 6" border
Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity	Full Cure	24 hours
Shelf Life		3 years
Flash Point		>200°F (93°C)
Caution!		Avoid contact with eyes and skin. In case of eye contact, flush eyes with plenty of water for at least 15 minutes. Wash thoroughly after handling. Do not take internally. If swallowed call a physician or Poison Control Center.
Safety Information		For additional information, see MSDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.