

Features

- Ideal for environments such as schools, offices, retail, healthcare facilities and other commercial spaces
- Popular center basket design with square or round (ADSM) lens
- Slim 2-3/8" profile fits restrictive plenums and optimizes pallet space
- Standard 0-10V dimming driver that dims to 10%
- Designed to provide 80% lumen maintenance at 60,000 hours



Ordering Information

Catalog Number	UPC	Description	Replaces Up To	Lumens	Input Watts	CCT	CRI	Voltage	Pallet Quantity
BLC 2X2 3300LM 35K	191848536469	2'x2' Center Basket LED Lay-in with Square Lens	2 U-Bent 32W T8	3,300	30W	3500K	80	120-277V	52
BLC 2X2 3300LM 40K	191848536506	2'x2' Center Basket LED Lay-in with Square Lens	2 U-Bent 32W T8	3,300	30W	4000K	80	120-277V	52
BLC 2X2 4000LM 35K	191848536544	2'x2' Center Basket LED Lay-in with Square Lens	2 U-Bent 32W T8	4,000	36W	3500K	80	120-277V	52
BLC 2X2 4000LM 40K	191848536551	2'x2' Center Basket LED Lay-in with Square Lens	2 U-Bent 32W T8	4,000	36W	4000K	80	120-277V	52
BLC 2X4 4000LM 35K	191848536575	2'x4' Center Basket LED Lay-in with Square Lens	2 Lamp 32W T8	4,000	32W	3500K	80	120-277V	26 CS
BLC 2X4 4000LM 40K	191848536629	2'x4' Center Basket LED Lay-in with Square Lens	2 Lamp 32W T8	4,000	32W	4000K	80	120-277V	26 CS
BLC 2X4 5000LM 35K	191848536636	2'x4' Center Basket LED Lay-in with Square Lens	2 Lamp 32W T8	5,000	43W	3500K	80	120-277V	26 CS
BLC 2X4 5000LM 40K	191848536599	2'x4' Center Basket LED Lay-in with Square Lens	2 Lamp 32W T8	5,000	43W	4000K	80	120-277V	26 CS
BLC 2X2 3300LM 35K ADSM	193048323177	2'x2' Center Basket LED Lay-in with Round Lens	2 U-Bent 32W T8	3,300	30W	3500K	80	120-277V	52 CS
BLC 2X2 3300LM 40K ADSM	193048323269	2'x2' Center Basket LED Lay-in with Round Lens	2 U-Bent 32W T8	3,300	30W	4000K	80	120-277V	52 CS
BLC 2X4 4000LM 35K ADSM	193048323443	2'x4' Center Basket LED Lay-in with Round Lens	2 Lamp 32W T8	4,000	32W	3500K	80	120-277V	26 CS
BLC 2X4 4000LM 40K ADSM	193048323511	2'x4' Center Basket LED Lay-in with Round Lens	2 Lamp 32W T8	4,000	32W	4000K	80	120-277V	26 CS
BLC 2X2 3300LM 80CRI 35K ADSM MIN10 ZT MVOLT EL14L	193048323191	2'x2' Center Basket LED Lay-in with Round Lens	2 U-Bent 32W T8	3,300	30W	3500K	80	120-277V	52
BLC 2X2 3300LM 80CRI 40K ADSM MIN10 ZT MVOLT EL14L	193048323351	2'x2' Center Basket LED Lay-in with Round Lens	2 U-Bent 32W T8	3,300	30W	4000K	80	120-277V	52
BLC 2X4 4000LM 80CRI 35K ADSM MIN10 ZT MVOLT EL14L	193048323429	2'x4' Center Basket LED Lay-in with Round Lens	2 Lamp 32W T8	4,000	32W	3500K	80	120-277V	26
BLC 2X4 4000LM 80CRI 40K ADSM MIN10 ZT MVOLT EL14L	193048323504	2'x4' Center Basket LED Lay-in with Round Lens	2 Lamp 32W T8	4,000	32W	4000K	80	120-277V	26


CS Denotes Contractor Select Product

Accessories

Catalog Number	UPC	Description
DGA24	784231089217	Drywall Grid Adapter for 2'x4' Recessed Fixture
DGA22	784231093818	Drywall Grid Adapter for 2'x2' Recessed Fixture
2X4SMKSH PAF	193047794312	2'x4' Surface Mount Troffer Kit
2X2SMKSH PAF	193047794299	2'x2' Surface Mount Troffer Kit
PS1050	888791760071	LED Emergency Battery Pack, 10W 50VDC (Non CEC Compliant)
PS1055LCP	191723518283	LED Emergency Battery Pack, 10W Constant Power, Self-Diagnostic, CEC compliant
ELA PSRME IC	889804999143	Remote Enclosure for Battery for Insulated Ceiling
RK1BDP U	193048492231	BDP (Ballast Disconnect Plug)

Dimensions

BLC 2'x4' Length: 47-3/4 (121.2)
 BLC 2'x2' Length: 23-3/4 (60.3)
 Width: 23-3/4 (60.3)
 Depth: 2-3/8 (6.0) All dimensions are inches (centimeters) unless otherwise specified.



Certain airborne contaminants can diminish integrity of acrylic. See page 162 for Acrylic Compatibility table for suitable uses.