



Technical Data

Color	Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	27.95 x 13.78 x 11.81
Case Weight (lbs)	19.84
Country of Origin	Malaysia
Lens	Tinted
Frame Style	Over-The-Glass
Lens Color	Gray
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Spatula
Base Curve	4
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

Bouton® Optical The Scout™ OTG Rimless Safety Glasses with Gray Temple, Gray Lens and Anti-Scratch Coating

- Polycarbonate unilens
- Over-the-glass design fits over all prescription eyewear
- Can also be worn by itself as a regular safety glass
- Molded nose bridge design to fit the vast majority of users
- Indirect vent temples to reduce fogging
- 4 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Fits Comfortably Over Personal Eyewear
- Outdoor Work
- Construction Applications
- Public Works

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-30

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-99-0900	Clear	Clear	Clear	AS	616314024771	01616314024771	02616314024771
250-99-0901	Gray	Tinted	Gray	AS	616314025143	01616314025143	02616314025143
250-99-0980	Clear	Clear	Clear	U	616314025136	01616314025136	02616314025136
250-99-0980DP	Clear	Clear	Clear	U	616314027598	01616314027598	02616314027598

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated