SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



62-8063 - Desmond; 30-Inch LED Pendant; 93 Watt; 2700K/3000K/3500K CCT; Smoked Bronze Finish; Alabaster Stone

90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 25,000 HOURS | 3 YEAR WARRANTY | 120-277V | IP 20

GENERAL

Company	NUVO
EA Height	8.1
EA Width	33.5
EA Length	33.5
Mounting Height	1.5
Mounting Length	8.25
Mounting Width	8.25
Bulb Included	Integrated
Material	Stainless Steel
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<20%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Desmond
Finish Family	Bronze
Amps	2.150A
Lens Finish	Alabaster
Lens Material	Alabaster Stone
Lensed	Yes
Power Factor	>0.9
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	235W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K
Dimmable	Yes-Dimmable
Hours Rated	25000
Beam Angle (degree)	120
Color Temp	Warm White to Neutral White
CRI	90+
Dimming Type	Phase cut
Operating Frequency	50/60Hz
Operating Temp	-4F to +140F (-20C to +60C)
Lumens	7440L
Volts	120V-277V
Watts	93W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Bronze
Housing Color	Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Square

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416446
Case Cube	5.2605
Case Height	8.1
Case Length	33.5
Case Quantity	1
Case UPC	10045923416443
Case Weight	50.3
Case Width	33.5
EA Cube	5.2605
EA Height	8.1
EA Length	33.5
EA Quantity	1
EA Weight	50.3
EA Width	33.5
Pack Type	Kraft Box
Web Height	4.13
Web Length	29.88
Web Width	29.88

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026