



TEGERA® 75

Learn more

SLEEVE WITH KEVLAR® FIBRE, CUT LEVEL D

Cut protection sleeve with cut resistance level D. 13 gg, made of Kevlar® fibre, polyester, spandex and steel fibre yarn. For all-round work, approved for handling foodstuffs and withstands contact heat up to 100°C. With unique hand-attachment for good fit and easy donning and doffing of gloves. Use together with a suitable glove for full protection.

CHARACTERISTICS

- High level of protection
- Flexible
- Comfortable
- Breathable

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs

Kevlar

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Cut risk environments

PRIMARY AREAS OF USE

Assembly, Building and construction, Engineering, Food handling, Glass industry work, Inspection work, Installation work, Machine operating, Metalwork, Warehouse work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Electrical equipment manufacturing, Food and beverage processing, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Heavy weight

SPECIFICATION

TYPE Cut resistant sleeves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL KEVLAR® fiber, Spandex, Stainless steel fibre yarn
LENGTH 420-490 mm
COLOUR Yellow
PIECES PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Bulk pack
FASTENING Elasticated 360°
CUT RESISTANCE (EN ISO 13997) Cut resistance level D
CUT RESISTANCE (EN ISO 13997) TDM: 19.4 N
OUTER MATERIAL SPECIFICATION Para-aramid, Polyester, Stainless steel fibre yarn, Elastane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 1X4XD

EN 407:2020 (No flame protection) X1XXXX

ANSI A4 CUT

ANSI 3 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
7	S	75-7	7340118438931
8	M	75-8	7340118348988
9	L	75-9	7340118349077
10	XL	75-10	7340118349169

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.