Highball | E21189-05GM

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Minimalist in form and futuristic in styling, a gradient color effect applied to cylindrical glass shades provides a dynamic lighting effect. A Polished Gunmetal LED housing supports the glass adds a mirror like effect to the highly reflective glass. The resulting effect is a replication of the LED light along the length of the glass. Available in a mirrored Gradient Smoke or Gradient Amber glass, the finishes remarkably coordinate with many interior color palettes.



*max overall height

MEASUREMENTS

DIMENSION	: 22.75" L x 22.75" W x 12.5" H
MAX OAH	: 130" OAH
CANOPY	: 22.75" W x 1.5" H x 22.75" L
HANGING WEIGHT	: 18 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 5,680 Rated (3,240 Del.)
BULB	: 9 x 8W LED DC Integrated , 72W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Gunmetal (GM)

GLASS

Amber 05

MATERIAL

Steel, Polycarbonate, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com