

PAINTED NO. 1

MDS300-PN/OW

Simple, easy, and approachable, the tried-and-true Painted No.1 pendant light is now available in even more beautiful color and finish combinations. The classic hues have a timeless appeal, each giving the curved shade a different feel. This versatile pendant light comes in a 3-light design with an Aged Brass and Soft Studio Green finish or Polished Nickel and Soft French Blue finish. The 4-light design is also available in these finishes, as well as Aged Brass and Darkest Blue; Polished Nickel and Off-White; and Aged Brass and Off-White.

FINISHES

POLISHED NICKEL w/ OFF-WHITE (MDS)

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 16"

Width/Diameter: 18.25"

Minimum Height: 21"

Maximum Height: 73.75"

Canopy/Backplate: 4.75"

Hanging Type: 54" Chain

Product Weight: 13.2lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: Yes

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: White Glass

Shade 1 Top Width: 17"

Shade 1 Height: 0.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 75

Bulb Quantity: 3

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 22" x 22" x 21"

Carton 1 Weight: 17lb

Shipping Method: Ground

Country of Origin: VN

