Tartan | E24814-82BCN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Inspired by patterned fabrics of the Scottish Highlands, the Tartan collection features a waving grid-like design etched deep into the transparent acrylic body. Hand-formed into a curling structure, the material gives the impression of billowing in the breeze. Color temperature selection at the canopy allows you to choose from Warm, Neutral, and Cool White colored LED lighting.



*max overall height

MEASUREMENTS

DIMENSION	: 32" L x 18" W x 10.5" H
MAX OAH	: 130" OAH
CANOPY	: 7" W x 1.5" H x 11" L
HANGING WEIGHT	: 10.56 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,000 Rated (1,250 Del.)
BULB	: 1 x 25W LED DC Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 30-35-40K

FINISHES OPTION

Brushed Champagne (BCN)

Polished Chrome (PC)

GLASS

Heavy Faceted 82

MATERIAL

Stainless Steel, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com