

Click-Torque XP 1 pre-set adjustable torque wrench for insert tools, 2.5-25 Nm, 2.5 Nm, 9x12 x 2.5 Nm x 2.5-25 Nm



EAN:	4013288206206	Size:	245x50x50 mm
Part number:	05075670010	Weight:	375 g
Article number:	Click-Torque XP 1	Country of origin:	TW
		Customs tariff number:	82041100

- Pre-set click torque wrench in unmistakable Wera design
- Audible and tactile release mechanism when the set torque value is reached
- Pre-set torque values can be changed within the metered range in the test laboratory
- Measuring range: 2.5-25 Nm; precise to $\pm 2\%$ as per DIN EN ISO 6789-1:2017-07
- With square socket (9x12 mm) for interchangeable plug-in tools; clockwise and anti-clockwise torque-control

Torque wrench with pre-set torque value for all applications where the same torque and repeat accuracy is required. The torque value can be changed within the metered range. The robust release mechanism guarantees a clearly audible and tactile trigger signal when the set torque value is reached. Square socket for interchangeable plug-in tools for clockwise and anti-clockwise torque-control. A presetting which deviates from this value to a desired torque value within the specified metered range is possible on request.

Web link
<https://www.wera.de/en/05075670010>

Wera - Click-Torque XP 1
05075670010 - 4013288206206

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Click-Torque XP 1 pre-set adjustable torque wrench for insert tools, 2.5-25 Nm, 2.5 Nm, 9x12 x 2.5 Nm x 2.5-25 Nm



Click-Torque Wrench series



We wanted working with torque wrenches to be simple and accurate which is why we developed the Click-Torque wrenches. With the ability to set and save the default values and with the unmistakable, robust Wera design, these torque wrenches are the ideal tools for all bolting applications that require torque-controlled tightening (clockwise torque wrenches) and tightening and loosening (torque wrenches for insert tools).

Click-Torque XP



The Click-Torque XP torque wrenches are provided with pre-set torque values. These tools are ideal for all applications where the same torque and repeat accuracy is required.

Drive 9x12 mm




For 9x12 mm interchangeable insert tools.

Exact




Precise to $\pm 2\%$ as per DIN EN ISO 6789-1:2017-07.

For right and left direction



The Click-Torque wrenches for insert tools are suitable for clockwise and counterclockwise uses.

Customised pre-setting



The Click-Torque XP torque wrenches with a pre-set torque value can be set to any value within the specified metered range in the test laboratory.

Web link

<https://www.wera.de/en/05075670010>

Wera - Click-Torque XP 1
05075670010 - 4013288206206

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Click-Torque XP 1 pre-set adjustable torque wrench for insert tools, 2.5-25 Nm, 2.5 Nm, 9x12 x 2.5 Nm x 2.5-25 Nm



Further versions in this product family:

						S_k	l_k														
	Nm	Nm	lbf. ft.	mm	mm	mm	mm	mm	mm	mm	mm	inch	inch	inch	inch	inch	inch	Nm	Nm	lbf. ft.	lbf. ft.
05075670001 ¹⁾	9x1 2	2.5	2.5- 25	2-1 8	217	17.5	180. 0	137	35	24	20	8 35 /64"	5 25 /64"	1 3/8"	15/1 6"	25/3 2"		2.5	25.0	2.0	18.0
05075670010 ^{2),1)}	9x1 2	2.5	2.5- 25	2-1 8	217	17.5	180. 0	137	35	24	20	8 35 /64"	5 25 /64"	1 3/8"	15/1 6"	25/3 2"		2.5	25.0	2.0	18.0

1) S_k = Actual dimension of the test attachment; l_k = Distance from the force application point to the test device axis
 2) Any presetting which differs from this value, can be set to a desired torque value within the specified metered range upon request. The desired settings can be made in the following units: Nm, kgf. m, lbf. ft., ozf. in., dN. m, kgf. cm, lbf. in, in. oz, cN. m, gf. m, ft. lb, gf. cm, in. lb.

Web link
<https://www.wera.de/en/05075670010>

Wera - Click-Torque XP 1
 05075670010 - 4013288206206

Wera Werkzeuge GmbH
 Korzelter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de