



Ironcat®

AR Premium Top Grain Cowhide Leather MIG Welder's Glove with Kevlar® Stitching & Para-Aramid Liner

- Top Grain Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Top Grain leather is smooth, provides durability and dexterity
- Gunn cut pattern delivers excellent durability, wear and comfort, especially for heavier gloves
- Para-Aramid blend lining provides added cut and heat resistance
- ARC Rating: ATPV 34 cal/cm2
- Wing thumb increases comfort in open-handed work
- Reinforced pulse protector
- Stitched with Kevlar® adding strength and burn resistance
- Gold split cowhide gauntlet cuff for added forearm protection and allows for easy on and off



Technical Data

Color	Natural
Sizes Available	S-2XL
Packaging	Pair Bagged Plain
Packed	6 Dozen/Case
Case Dimensions (in)	21.50 x 14.02 x 15.00
Case Weight (lbs)	41.25
Country of Origin	Pakistan
Hide	Top Grain Cowhide
Lining	Aramid
Grade	Premium
Cuff	Gauntlet
Palm	Leather
Back	Leather
Closure	Slip On
Thumb	Wing
Stitching	Kevlar
Construction	Cut-and-Sewn, Extended Cuff, Gunn Cut

Performance Data

ARC Rating	34 cal/cm2
ARC Rating	34 cal/cm2
Cut Level	A4
Cut Level	A4
ANSI Puncture Level	3
ANSI Puncture Level	3

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
6040/S	Natural	S	616314354359	10616314354356	20616314354353
6040/M	Natural	M	616314380389	10616314380386	20616314380383
6040/L	Natural	L	616314380341	10616314380348	20616314380345
6040/XL	Natural	XL	616314380426	10616314380423	20616314380420
6040/2XL	Natural	2XL	616314380303	10616314380300	20616314380307