

## 4" Line Voltage Trims

The trims shown here may be used with 4" R/PAR20 Universal housing on page 104.

### Downlights



**Pinhole with Integral Shield**  
**13 WH**  
 IC1: 30W R20, 35W PAR20  
 IC1P/TC: 50W PAR/R20  
 IC1P: 40W K19  
 2" Aperture



**Baffle**  
**14 WWH** White  
**14 BBL** Black  
**14 BWH** Black  
**14 BABZ** Black  
**14 BSC** Black  
 IC1: 50W PAR20  
 (Requires T599  
 Socket Extender),  
 50W R20  
 IC1P/TC1/TC1R: 50W  
 PAR/R20  
 3 3/8" Aperture



**PAR20/R20 Cone**  
**17 BWH** Black Alzak®  
**17 CWH** Clear Alzak®  
**17 GWH** Gold Alzak®  
**17 HZWH** Haze  
**17 PTSC** Pewter Alzak®  
**17 WWH** Gloss White  
**17 WHZABZ** Wheat Haze  
**17 WHZWH** Wheat Haze  
 IC1/IC1P/TC1/TC1R:  
 50W PAR/R20  
 IC1P: 60W K19  
 3 3/8" Aperture

### Adjustables



**Gimbal Ring**  
**10 ABZ**  
**10 BL**  
**10 SC**  
**10 WH**  
 IC1P/TC: 50W PAR20;  
 75W ES20 (120V GU10)  
 Adjustment: PAR20=25°,  
 ES20=35°



**Mini Eyeball PAR16**  
**18 SC**  
**18 WH**  
 40W R16  
 60W PAR16  
 Adjustment: 35° vertical



**Mini Eyeball**  
**19 WH**  
 IC-25W R14; TC-40W R14,  
 40W R16  
 (Intermediate screw base lamp)  
 Adjustment: 35° vertical



**Flush Gimbal Ring**  
**440 WH**  
**440 BL**  
**440 SC**  
**440 ABZ**  
 35W MR16/ES16 GU10 base  
 (Requires GU10WHIP)



**Slot**  
**445 WH**  
 50W MR16/ES16 120V GU10  
 base (Not used with IC1).  
 (Requires GU10WHIP)  
 Adjustment: 40° vertical



**Eyeball with Black Baffle**  
**448 WH**  
**448 SC**  
 35W MR16/ES16 GU10 base  
 (Requires GU10WHIP)

### Wall Wash



**Scoop**  
**16 WH**  
 IC-25W R14; TC-40W R14,  
 40W R16  
 (Intermediate screw base  
 lamp) Adjustment: 50° vertical

**Scoop**  
**446W**  
 50W MR16/ES16 120V GU10  
 base (Not used with IC1)  
 (Requires GU10WHIP)  
 Adjustment: 40° vertical

### Lensed



**Frosted Lens with Clear Center**  
**12 WABZ**  
**12 WSC**  
**12 WWH**  
 IC1: 30W R20,  
 50W PAR20 with 1"  
 socket extender #T599  
 IC1P/TC: 50W PAR/R20  
 IC1P: 40W K19



**Drop Opal**  
**11 WH**  
 IC1: 30W R20,  
 35W PAR20  
 IC1P: 30W R20,  
 50W PAR20, 40W K19  
 TC: 50W PAR/R20

### Squares



**Downlight**  
**17SQ HZWH** Haze  
**17SQ WWH** White  
**17SQ BWH** Black  
**17SQ WHZWH** Wheat Haze  
 50W PAR20 (Requires T599  
 socket extender), 39W  
 PAR20, 30W R20



**Flush Gimbal**  
**440SQ WH**  
**440SQ BL**  
 35W MR16 120V  
 (Requires GU10WHIP).  
 Adjustment: 35° vertical



**Pinhole**  
**13SQ WH** White  
 50W PAR20 (Requires T599  
 socket extender), 35W PAR20,  
 30W E20



**Frosted Lens with Clear Center**  
**12SQ WWH** White  
 50W PAR20  
 (Requires T599 socket  
 extender), 30W R20



### Trim Ring Finishes

**ABZ** Classic Aged Bronze  
**SC** Satin Chrome  
**WH** White  
**BL** Black