



Technical Data

Color	Black
Sizes Available	M-XL
Polymer	Butyl
Thickness	32 Mil
Lining	Unlined
Dip	Single
Length	14"
Cuff	Rolled
Grip	Rough
Construction	Unsupported, Waterproof
Case Dimensions (in)	32.00 x 21.00 x 15.00
Case Weight (lbs)	20.00
Packed	72 Pair/Case
Packaging	Pair Bagged Plain
Certifications	TAA Compliant, Latex Free
Country of Origin	United States

North® Butyl™

32 Mil Butyl Rubber Glove with Rough Grip - 14"

- Exceptional resistance to a broad range of toxic chemicals: making it the only suitable for many critical applications
- Highly resistant to ketones (MEK: MIBK: acetone) and esters (tricresyl phosphate: amyl acetate: ethyl acetate)
- Solvent based: multi-dip manufacturing process provides multiple layers of polymer (like a glove within a glove) which results in a glove of superior quality
- Butyl provides the highest permeation resistance to vapors and gases

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
B324R/8	Black	M	821812008721	821812008714	00821812008707
B324R/9	Black	L	821812008752	821812008745	00821812008738
B324R/10	Black	XL	821812008660	821812008653	00821812008646
B324R/11	Black	2XL	821812008691	821812008684	00821812008677