



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**S14207** - 5.5 Watt ST19 LED; 2000K CCT; Medium Base; Clear Glass; Amber Coil Filament; Dimmable; 120 Volt



**GENERAL**

Company	SATCO
EA Height	5.89
EA Width	2.5
EA Length	2.5
Dimmable Text	Forward or Reverse Phase; Line Voltage
Lamp Filament	Spiral
Material	Glass
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	<75%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Clear
Amps	0.076A
Lens Material	Glass
Operating Position	Universal
Power Factor	>0.7
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	40W

**ELECTRICAL**

CCT (Kelvin Temp)	2000K
Dimmable	Yes-Dimmable
Hours Rated	15000
Beam Angle (degree)	300
Color Temp	Warm White
CRI	90+
Dimming Type	Linear Dimming, Phase cut
Operating Frequency	60Hz
Operating Temp	-25C (-13F) to +40C (+104F)
Lumens	500L
Volts	120v
Watts	5.5W

**PHYSICAL**

Lamp Base	Medium
Finish	Clear Amber
ANSI Base	E26
Lamp Type	ST19
MOD Lamps	2.29
MOL	5.32

**ADDITIONAL INFO**

Warranty	2-Years
Rated For Enclosed Fixture	Yes

**PACKAGING**

UPC	045923142079
Case Cube	0.7256
Case Height	6.82
Case Length	16.43
Case Quantity	24
Case UPC	10045923142076
Case Weight	4.47
Case Width	11.19
EA Cube	0.0213
EA Height	5.89
EA Length	2.5
EA Quantity	1
EA Weight	0.13
EA Width	2.5
Inner Cube	0.1597
Inner Height	6.5
Inner Length	7.92
Inner Quantity	6
Inner UPC	20045923142073
Inner Weight	0.97
Inner Width	5.36
Pack Type	Color Box
Web Length	5.32
Web Width	2.29

**COMPLIANCE**

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
Title 20	Exempt
T24 Compliant	No