

Project Name

Location

Prepared By



## SATCO S11897

13WLED/DLR/6/FS/WR/RND/WH

**Notes**

(www) 06-11-2023 09:31:01

**General**

|                           |                               |
|---------------------------|-------------------------------|
| Status                    | Active                        |
| Recessed Can Size         | 6 in.                         |
| Wattage                   | 9W/11W/13W                    |
| Voltage                   | 120V                          |
| Finish                    | Matte White                   |
| CCT (Kelvin)              | 2700K/3000K/3500K/4000K/5000K |
| Color Temperature         | Warm White to Natural Light   |
| Lumen Output              | 900L/1200L/1400L              |
| Indoor or Outdoor Fixture | Indoor                        |

**Specifications**

|                       |                            |
|-----------------------|----------------------------|
| Technology            | LED                        |
| CRI                   | 90+                        |
| Beam Angle            | 110                        |
| Rated Hours           | 50000                      |
| Operating Temperature | -20C (-4F) to +40C (+104F) |
| Dimmable              | Yes-Dimmable               |
| Sloped Ceiling        | No                         |

**Dimensions**

|              |      |
|--------------|------|
| Width (in.)  | 7.28 |
| Height (in.) | 2.56 |
| Weight (lb.) | 0.56 |

**Compliance**

|                      |                               |
|----------------------|-------------------------------|
| Safety Listing       | cETLus - Classified           |
| Location Rating      | Wet                           |
| ENERGY STAR          | Yes                           |
| ES Unique ID         | ESID-3994241                  |
| Air Tight Rated      | Yes                           |
| IC Rated             | Yes                           |
| California Status    | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale               |
| California Prop 65   | Lead                          |
| RoHS Compliant       | Yes                           |
| FCC Compliant        | Yes                           |
| SDS Sheet            | LED_Fixture                   |

**Additional Information**

|                    |  |
|--------------------|--|
| Specification Note | Default CCT setting is 2700K; Default Wattage setting is 11W |
| Warranty           | 5-Years  |