

Project Name

Location

Prepared By



SATCO S11201

3.5T14/CL/930/120-240V/E27/CD

Notes

[www] 04-30-2023 09:43:57

General

Status	Active
Watts	3.5W
Incandescent Equivalent	35W
Volts	120V-240V
Shape	T14
Base	European Medium
ANSI Base	E27
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	90+
Lumens	420L
Beam Spread	360
Dimmable	Non-Dimmable
Hours Rated	25000
Technology	LED

Electrical

Operating Frequency	60HZ
Candlepower	50
Power Factor	>0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	2.48
MOD	1.06
Housing Color	White
Weight (lb.)	0.12

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Years

Compliance

Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp