Fuse | E23442-10BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Within the void of clear glass, a white cylindrical tube of LED light extends in two directions. The evenly distributed light source can be adjusted to 5 selectable color temperatures, from warm 2700k to a cool 5000K and neutral white light sources in between. Available in three finish options: matte Black, Natural Aged Brass, and Polished Chrome, these sconces are great for use in bathrooms and along corridors with extensions less than 4 inches for ADA compliance.



MEASUREMENTS

DIMENSION	: 23.25" W x 1.75" H x 3.25" Ext
BACK PLATE	: 4.75" W x 6.25" H x 11.5" HCO
HANGING WEIGHT	: 2.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,000 Rated (600 Del.)
BULB	: 1 x 13W LED DC Integrated , 13W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Only at 120V with Triac
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: All

FINISHES OPTION

Black (BK)
Natural Aged Brass (NAB)
Polished Chrome (PC)

GLASS

Clear and White 10

MATERIAL

Steel

RATINGS

cETLus
Damp Location
CA Title 24
ADA

ADDITIONAL

INSTALL UP/DOWN: Horizontal/Vert
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com