

# HOM240CP

Mini circuit breaker, Homeline, 40A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL



## Main

|                              |                                  |
|------------------------------|----------------------------------|
| Product                      | Miniature circuit-breaker        |
| Range                        | Homeline                         |
| Current Rating               | 40 A                             |
| Certifications               | UL Listed                        |
| Voltage Rating               | 120/240 V AC                     |
| Mounting Type                | Plug-in                          |
| Number of Poles              | 2P                               |
| Short Circuit Current Rating | 10 kA                            |
| Number of Spaces             | 2                                |
| Circuit Breaker Type         | Standard                         |
| Ratings                      | HACR rated                       |
| Electrical Connection        | Box lugs                         |
| Wire Size                    | AWG 8...AWG 2 aluminium/copper)1 |
| Type of Packing              | Consumer packaging               |

## Complementary

|                   |  |
|-------------------|--|
| Tightening torque | 40.71 lbf.in (4.6 N.m) (AWG 8...AWG 2) |
| Height            | 3.13 in (79.50 mm)                     |
| Width             | 2 in (50.80 mm)                        |
| Depth             | 2.98 in (75.69 mm)                     |

## Environment

|                                       |                |
|---------------------------------------|----------------|
| Ambient Air Temperature for Operation | 104 °F (40 °C) |
|---------------------------------------|----------------|

## Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 01346-HOM 2 POL BULK BRKR 15-60A |
| Discount Schedule | CPH                              |
| GTIN              | 047569062780                     |
| Returnability     | Yes                              |
| Country of origin | MX                               |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 2.00 in (5.08 cm)    |
| Package 1 Width              | 3.00 in (7.62 cm)    |
| Package 1 Length             | 3.10 in (7.874 cm)   |
| Package 1 Weight             | 11.20 oz (317.515 g) |
| Unit Type of Package 2       | PAL                  |
| Number of Units in Package 2 | 1800                 |
| Package 2 Height             | 40.00 in (101.6 cm)  |
| Package 2 Width              | 40.00 in (101.6 cm)  |
| Package 2 Length             | 48.00 in (121.92 cm) |

|                              |                             |
|------------------------------|-----------------------------|
| Package 2 Weight             | 1332.00 lb(US) (604.185 kg) |
| Unit Type of Package 3       | BB1                         |
| Number of Units in Package 3 | 5                           |
| Package 3 Height             | 3.40 in (8.636 cm)          |
| Package 3 Width              | 3.00 in (7.62 cm)           |
| Package 3 Length             | 3.70 in (9.398 cm)          |
| Package 3 Weight             | 3.65 lb(US) (1.656 kg)      |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |