



SWC1926



69.75" x 23.63" x 26.63" (H x W x D)

171 bottle single-zone commercial wine cellar designed for the display and refrigeration of beverages, with glass door, digital thermostat, and black cabinet

Highlights:

- Digital thermostat offers precise temperature control
- Stores up to 171 Bordeaux bottles on classic wooden shelves
- Factory installed lock provides security you can depend on

Product Features:

Large capacity	Interior can hold up to 171 standard 750ml Bordeaux style bottles. If using this wine cellar for wider Burgundy style bottles, you can hold up to 128. For champagne, the interior can hold 14 bottles (plus an additional 154 of the standard Bordeaux style)
Double pane tempered glass door	Slightly tinted glass provides full view of interior, with a stainless steel trim for added accent
Commercial design	Meets UL-471 commercial standards
Digital thermostat	Intuitive electronic controls make it easy to manage the internal temperature of your collection
LED lighting	Recessed lighting offers an elegant, efficient view of your collection
Slide-out wooden shelves	15 wooden wine shelves for classic storage
Factory installed lock	Keyed lock for trusted security
Reversible door	User-reversible door swing allows for more flexibility in placing the unit
Fully finished black cabinet	Allows the unit to be used freestanding



SWC1926 Specifications:

Overview	
Nominal Height	70.0" (178 cm)
Height of Cabinet	69.75" (177 cm)
Nominal Width	24.0" (61 cm)
Width	23.63" (60 cm)
Nominal Depth	27.0" (69 cm)
Depth	26.63" (68 cm)
Depth with Handle	27.75" (70 cm)
Depth with door at 90°	48.75" (124 cm)
Bottles	171 bottles
Defrost Type	Automatic
Door	Glass
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.7
Voltage/Frequency	115 V AC/60 Hz
Weight	187.0 lbs. (85 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101031965
Wine Cellar	
Number of Zones	1
Door Swing	RHD
Reversible	Yes
Shelf Type	Wood
Shelf Qty	15
Thermostat Type	Digital
Interior Light	Yes
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	1.91 oz.
High Side PSI	270.0
Low Side PSI	105.0
Interior Height 1	60.5" (154 cm)
Interior Width 1	19.75" (50 cm)
Interior Depth 1	21.0" (53 cm)
Compressor Step Height	3.75" (10 cm)

Compressor Step Width	19.75" (50 cm)
Compressor Step Depth	5.5" (14 cm)
Sabbath Mode	Yes
Sound Level	34 dB



